

Electrical conductivity measurement of non-ferrous metals enters a new dimension

The electrical conductivity is an important material property that not only informs about how well a metal conducts electrical current but also provides information about its composition, microstructure or mechanical properties.

The SIGMASCOPE® SMP10 provides excellent features for measuring these characteristics. Signal evaluation based on established physical knowledge, the latest instrument technology and software for simple handling provide the ideal basis for such measurements.

NDT INTERNATIONAL INC.
711 S. Creek Road,
West Chester PA U.S.A.
19382-8013




Tel: (610) 793-1700
Fax: (610) 793-1702
Info@ndtint.com
www.ndtint.com




Measurement principle, application and hardware

Measurement principle

The SIGMASCOPE® SMP10 measures the electrical conductivity using the eddy current method according to DIN EN 2004-1 and ASTM E 1004. The phase-sensitive measurement signal evaluation enables a contact-free determination of the electrical conductivity, for example, under paint or synthetic coatings of up to 500 µm in thickness. This also minimizes the influence of surface roughness.



The eddy currents generated by the magnetic field of the probe and utilized as the measurement effect are influenced by the electrical conductivity.



The penetration depth δ of the eddy currents is established by the measurement frequency f , which determines the minimum permissible thickness of the specimen.

Applications

- Measurement of the electrical conductivity of all non-magnetic metals, even stainless steel, EURO coins, etc.
- Measurement of the hardness and strength of heat-treated materials, e.g., aluminum alloys; inspection for heat damage.
- Measurement of the phosphor content in copper.
- Monitoring of deposition processes, e.g., for Cu-Cr-alloys.
- Determination of the degree of purity.
- Verifying the homogeneity of alloys.
- Scrap metal sorting.



The electrical conductivity measurement is employed for the production, processing or inspection of finished goods (e.g., EURO coins) made of NF metals.



The electrical conductivity measurement is an important quality assurance component in the manufacture, maintenance or repair of airplanes.

Hardware

The SIGMASCOPE® SMP10 is a compact, ergonomic portable instrument with a shock-resistant synthetic housing, a large, backlit LCD screen and a user-friendly keyboard with direct access to the most important measurement functions. The corresponding measurement probe ES40 is suitable for all four measurement frequencies of 60 kHz to 480 kHz. For automatic temperature compensation of the conductivity measurement (referenced to 20°C), the surrounding temperature or the current temperature of the specimen can be measured using either the temperature sensor integrated in the probe or an optional external sensor.



Hard shell case for transporting and storing the SIGMASCOPE® SMP10 including the required accessories (plug-in type AC adaptor, calibration standards, external temperature sensor and MPG stand).



The MPG stand is available for convenient use of the SIGMASCOPE® SMP10 in the lab. The optional MPG charging station is used to charge a spare rechargeable battery pack.

Calibration standards

A high-precision measurement is required to determine the electrical conductivity. Accurate standards are required to calibrate the instrument because the measurement is a comparison using the eddy current method. These standards are available in certified versions for the entire conductivity range. Special standards are also available for testing EURO coins, for example.



Certified standards for calibrating the SIGMASCOPE® SMP10 are traceable to internationally recognized calibration standards.



Internationally recognized Boeing Standards are used to establish the working standards of the SIGMASCOPE® SMP10.

Features

- Standard measurement according to ASTM E 1004 and DIN EN 2004-1.
- Menu-driven operator guidance.
- 100 application memories for calibrations and 20,000 measurement data.
- Diameter independent measurement on cylindrical parts through input of curvature radius.
- Automatic determination of temperature coefficient for the el. conductivity of aluminum alloys, by material selection or direct coefficient input.
- Measurement capture: automatic, continuous or with external start.
- Fast analog display.
- 3-stage measurement resolution.
- Graphical presentation of the specification limits on the display.
- Extensive statistical evaluation of test series with date and time capture.
- Display modes: scientific, statistic or simple.
- Current saver function.
- Automatic shut-off function.
- Temp. input: manual or automatic.
- Monitoring of the temperature change over time ($\Delta T/\Delta t$).
- Alarm function for the absolute temperature deviation.
- Master calibration using 8 standards.
- Corrective calibration using a maximum of 4 standards.
- Acoustic signal for measurement capture and violation of specification limits.
- 5 display languages (D, GB, F, I, E).

Technical Data

- Ergonomically shaped robust housing; user-friendly keyboard.
- Large backlit LCD display.
- Measurement frequencies:
SMP10: 60, 120, 240 and 480 kHz with probe ES40.
SMP10-HF: 60, 240, 480 kHz with probe ES40 and 1250 kHz with probe ES40-HF.
- Measurement range: 0.3 - 63 MS/m, or 0.5 - 108 %IACS.
- Measurement accuracy at +20°C: $\leq 1\%$ (1 - 100 % IACS).
- Up to 16 measurements per sec.
- Lift-off-compensation up to 0.5 mm.
- Smallest diameter of the measurement area: 11 mm
- Probe-integrated or optional external temperature sensor for the temperature compensation of the electrical conductivity measurement.
- RS232 interface.
- NiCd battery for operating time of approx. 20 h.
- Operating temperature: 5°C to 50°C.
- Mass incl. battery: 600 g / 21 oz.
- Dimensions: L x W x H 230 x 95 x 55 mm / 9.1" x 3.7" x 2.2".

Based on the user-friendly software menus, the user can quickly and easily select the instrument settings required for the measurement application, perform evaluations and present the measurement results in the desired manner. Not only in a numeric format but also in a graphical format with inserted specification limits or as a histogram.

In the standard measurement mode, the display shows the number of measurements n and the temperature used for temperature compensation and the electrical conductivity compensated to 20°C incl. the unit of measurement and the measurement frequency. In the statistics display mode, the display also provides information about the running mean value and the standard deviation.

In the scientific display mode, the temperature (taken by the sensor), the temperature coefficient or the selected material used for the temperature compensation of the electrical conductivity are displayed in place of the mean value and the standard deviation. Additional instrument functions can be selected by using the softkeys in the lower LCD region.

The simple display mode is available for applications where only the current display of the electrical conductivity and the number of performed measurements is of interest. The temperature compensation of the conductivity can be activated in this mode of operation as well.



Ordering Data

Product	Order no.	Product	Order no.
SIGMASCOPE® SMP10*	603-231	Calibration standards	
Probe ES40 (60, 120, 240, 480 kHz)	603-235	CAL-S SMP Titanium LT31	600-378
SIGMASCOPE® SMP10-HF*	603-403	CAL-S SMP Nickel silver	600-379
Probe ES40 (60, 240, 480 kHz)	603-235	CAL-S SMP Bronze	600-380
Probe ES40HF (1250 kHz)	603-401	CAL-S SMP Nordic Gold	602-603
Optional accessories		CAL-S SMP Brass	600-381
Temperature sensor SMP10	603-237	CAL-S SMP Al 2024/T3511	600-373
Battery pack MPG	603-232	CAL-S SMP Al 7175/T7351	600-374
Charging station MPG 230 V	603-245	CAL-S SMP AlMgSi F32	600-375
Charging station MPG 110 V	603-269	CAL-S SMP Al 99.5	600-376
Printer FMP3040	602-890	CAL-S SMP Cu 58 MS/m	600-377
PC-DATEX for EXCEL	602-465		
PC-DATACC for ACCESS	603-028		
Interface connection set MP	602-341		

* Including delivery: Carrying case, Stand MPG, Plug-in AC converter 110/230V, Cu reference standard with certificate.

The Institute for Electronics and Measurement Technology HELMUT FISCHER in Sindelfingen/Germany is an innovative leader in the field of coating thickness measurement, material analysis, microhardness testing, electrical conductivity- and ferrite content measurement as well as for density and porosity testing. The company is able to recommend the best solution for any appli-



cation. A comprehensive range of products is offered using X-ray fluorescence; Beta-backscatter; Magnetic; Magnetic induction; Electric resistance; Eddy current and Coulometric techniques. HELMUT FISCHER has 13 subsidiary companies and 32 marketing agencies strategically located around the globe.



FISCHERSCOPE® X-RAY XAN energy dispersive spectrometer for quantitative material analysis from A(Z=13) to U(Z=92).

The high quality standard of FISCHER instruments is the result of our efforts to provide the very best instrumentation to our customers.



FISCHERSCOPE® HM2000 with WIN-HCU® for the measurement of the microhardness HM according to ISO 14577.

FISCHER is a reliable and competent partner, offering expert advice, extensive service, and training seminars.



FERITSCOPE® MP30E for standardized non-destructive measurement of the ferrite content in austenitic welded products or in duplex steel.

Today, FISCHER instruments are used successfully in all technological fields of industry and research.

© Helmut Fischer GmbH + Co.KG

Subjects to changes

912-033

Printed in Germany

04/06

Helmut Fischer GmbH+Co.KG
Industriestraße 21
71069 Sindelfingen, Germany
Tel. (+49) 70 31 303-0
Fax (+49) 70 31 303-79
mail@helmut-fischer.de
Internet: www.Helmut-Fischer.com



Accredited acc. to
DIN EN ISO/IEC 17025



Accredited according to
DIN EN ISO 9001:2000
Germanischer Lloyd
Certification

Fischer Instrumentation (G.B.) Ltd.
Gordleton Industrial Park
Hannah Way, Pennington
Lymington/Hampshire SO41 8JD, England
Tel. (+44) 1590-684100, Fax (+44) 1590-684110
Internet: www.fischergb.co.uk
E-Mail: mail@fischergb.co.uk



Fischer Technology, Inc.
750 Marshall Phelps Road
Windsor, Ct. 06095, USA
Tel. (+1) 860 683-0781, Fax (+1) 860 688-8496
Internet: www.fischer-technology.com
E-Mail: info@fischer-technology.com



Sole Agent for Helmut Fischer GmbH+Co.KG, Germany:

Helmut Fischer Elektronik und Messtechnik AG
CH-6331 Hünenberg, Switzerland
Tel. (+41) 41 785 08 00, Fax (+41) 41 785 08 01
E-Mail: switzerland@helmutfischer.com

Branch Offices of Helmut Fischer AG, Switzerland:

Fischer Instrumentation Electronique
78180 Montigny le Bretonneux, France
Tel. (+33) (0) 1 30 58 00 58, Fax (+33) (0) 1 30 58 89 50
E-Mail: france@helmutfischer.com

Helmut Fischer S.R.L., Tecnica di Misura
20128 Milano, Italy
Tel. (+39) 02 255 26 26, Fax (+39) 02 257 00 39
E-Mail: italy@helmutfischer.com

Fischer Instruments, S.A.
08018 Barcelona, Spain
Tel. (+34) 93 309 79 16, Fax (+34) 93 485 05 94
E-Mail: spain@helmutfischer.com

Helmut Fischer Meettechnik B.V.
5627 GB Eindhoven, The Netherlands
Tel. (+31) 40 248 22 55, Fax (+31) 40 242 88 85
E-Mail: netherlands@helmutfischer.com

Fischer Instruments K.K.
Saitama-ken 340-0012, Japan
Tel. (+81) 48 929 3455, Fax (+81) 48 929 3451
E-Mail: japan@helmutfischer.com

Fischer Instrumentation (Far East) Ltd.
Kwai Chung, N.T., Hong Kong
Tel. (+852) 24 20 11 00, Fax (+852) 24 87 02 18
E-Mail: hongkong@helmutfischer.com

Fischer Instrumentation (S) Pte Ltd.
Singapore 118529, Singapore
Tel. (+65) 62 76 67 76, Fax (+65) 62 76 76 67
E-Mail: singapore@helmutfischer.com

Nantong Fischer Instrumentation Ltd.
Shanghai 200437, P.R.C., China
Tel. (+86) 21 6555 7455, Fax (+86) 21 6555 2441
E-Mail: china@helmutfischer.com

Fischer Measurement Technologies (India) Pvt. Ltd.
Pune 411036, India
Tel. (+91) 20 2682 2065, Fax (+91) 20 2682 2075
E-Mail: india@helmutfischer.com



ISO 9001
SOS Registration
No 11899
Valid for Fischer AG and Branch Offices

